

puricare

HERON COUNTER TOP

Hot | Room | Cold

 10 Ang Mo Kio Street 65 #05-12 Techpoint (Lobby B)

 Singapore 569059

 Office: 6742 1629

 Whatsapp: 83835166

puricare.sg.com

(f) facebook.com/puricaresg

instagram.com/puricaresg





FILTRATION SYSTEM

Heron has an integrated multi-stage filtration system and post-UV LED steriliser to remove chlorine. bacteria. odours and inorganic impurities. This is to ensure clean and pure water that is safe to drink at all times.



LED DISPLAY PANEL

Time Indicator

Local time will be displayed on the LED screen.

Hot Water Press this button to select hot water (92°C). A red light will also be lit at the water outlet point to indicate and warn that hot water is dispensing

Extra Hot / Reboiling

Button Press this button to start and close the reboil function When the reboiling function is activated the button shows red until hot water reaches the setting temperature (95°C), and the button light turns back to white again, default light on white

08:00

Press this button to select the Press this button to dispense volume of the water to be dispensed (180ml | 220ml | 1000ml.

puricare

UV Sterilization

Press this button to perform settings for the LIV sterilization

Cold Water

dispensina.

water outlet point to

Water Volume

indicate that cold water is

Press this button to dispense

cold water (7-10°C). A blue light will also be lit at the

SPECIFICATIONS + Heron is a stylish and compact water

dispenser that provides you with purified and clean water. The system is slim, smart and safe for everyday use. Heron provides you with hot (92°C-95°C), room (30-45°C), and cold water (7-10°C). It features an ergonomic touch UI panel giving you multiple options for water temperature and volume. It also incorporates "Twish-N-Turn" filters and a post-UV LED steriliser.

Dimension	W190 x D450x H400	
Weight	18kg	
Colour	Black	
Filtration	Multi-stages	
Power	Hot 500W	Cold80W
Capacity	Hot 13L/Hr	Cold 10L/Hr
Voltage	230Vac	50Hz
Water Pressure	0.1 MPa - 0.4MPa	
Refrigerant	R134a	
Compressor	Single phase motor	

sterillizer



volumes control

indicator





All products listed in this brochure are solely distributed by Puricare Pte Ltd

Dispense Water

water upon selecting the temperature and volume To dispense room temperature water (30-45°C), press this button without selecting any temperature. Refrain from placing finger at the water outlet point as both cold and hot water will be dispensed one after another